




APPLICATION			LTR	E.C.O. NO.	BY	APP.
USED ON	NEXT ASSY.	QTY.	A	158015	1/2/82	MM



- NOTES:
- 1) COLOR: CABINET & TOP COVER = BLACK
PANELS & SIDE COVER = TAN
 - 2) MAXIMUM EXTERNAL AMBIENT TEMPERATURE 50°C AT INTAKE.
 - 3) TERM BARS MATE WITH THOMAS & BETTS 600V COPPER CABLE "LOCKTITE" CONNECTORS OR EQUIVALENT FOR I/O THRU .500MCM CABLE.
 - 4) OPTION FEATURES:
 - 1) BASE MOUNTING
 - 2) CASTORS
 - 3) I BEAM



MTL:	TOL:	DWN:	DATE:		ELECTRONIC MEASUREMENTS INCORPORATED
FIN:	P/L:	APP:	DATE:		
	459		1-31-80	TITLE:	DIMENSIONAL OUTLINE
				EMHP SIZE I	
				DWG. NO.	02-459-002
				REV.	A