




Features

- (1) For equipment designed to conform EMI regulations such as VCCI, CISPR, FCC, VDE, etc.
- (2) Attenuates conductive emission from power supply
- (3) Leakage current: 1mA max. (250V, 60Hz)
- (4) High shielded effect
- (5) Compact and light weight

Safety Standard


- UL1283, CSA Std. C22. 2 No. 8
- VDE0565 Teil. 3

Specifications


Item	Model	MYS-1215-22	MYS-1220-22
1	Rated voltage (AC, DC)	250V	
2	Rated current (AC, DC) (Note)	15A	20A
3	Test voltage (terminal to case, AC 1 minute)	2500V	
4	Isolation resistance (terminal to case, 500VDC)	100MΩ min.	
5	Leakage current	125V, 60Hz	0.5mA max.
		250V, 60Hz	1mA max.
6	DC resistance	0.03Ω max.	0.02Ω max.
7	Temperature rise	30°C max.	
8	Operating temperature range	-25 ~ +85°C	
9	Weight (typ)	310g	

(Note) : Value at Ta ≤ 55°C. Refer to the derating curve shown below at Ta > 55°C.



Circuit



Derating



Outline drawings



- Request customer specification for further details of specifications, outline, characteristics, etc. Read the instruction manual before usage.
- Contact us about delivery before ordering.


Case: Metal

(Unit: mm)

CHARACTERISTICS

■ Typical Insertion Loss Symmetrical
———— Asymmetrical

MYS-1215



MYS-1220

