




| APPLICATION |            |      | LTR | E.C.O. NO.           | BY       | APP. |
|-------------|------------|------|-----|----------------------|----------|------|
| USED ON     | NEXT ASSY. | QTY. | A   | REL TO MFG.          | 3/94     | WJW  |
|             |            |      | B   | ADDED DIMS/REAR VIEW | 7/97     | GFS  |
|             |            |      | C   | ECO16952             | 12/18/97 | RHS  |




- STANDARD FEATURES:
1. U/L RECOGNIZED INPUT CIRCUIT BREAKER.
  2. ANALOG VOLTMETER AND AMMETER.
  3. VOLTAGE AND CURRENT ADJUST.
  4. VOLTAGE AND CURRENT MODE LAMP INDICATORS.
  5. INTERNAL LINE FILTER.
  6. PWM CONTROL.
  7. REMOTE TURN ON AC,DC, OR DRY SWITCH
  8. P/S WEIGHT = 107 LBS.

| AC INPUT CHART |           |
|----------------|-----------|
| TB1            | 3Ø        |
| 1              | L1 INPUT  |
| 2              | L2 INPUT  |
| 3              | L3 INPUT  |
| 4              | N NEUTRAL |
| 5              | GROUND    |

(USED ON 380VAC INPUT ONLY)

(4) 8-32 PEMNUTS EACH SIDE FOR CHASSIS  
SLIDE OPTION (JONATHAN MFG #370-22)

J1 PROGRAMMING  
DB 25 CONN.(FEM.)  
FACTORY WIRED MATING CONNECTOR FOR  
LOCAL OPERATION PROVIDED.



|             |       |                 |             |                    |
|-------------|-------|-----------------|-------------|--------------------|
| MTL:        | TOL:  | PRJ: ENG: DATE: | DWN: DATE:  | ELECTRONIC         |
| SS 7/18/97  | ±.031 | SS 7/18/97      | JKA 9/3/92  | MEASUREMENTS, INC. |
| FIN:        | P/L:  | MFG. DATE:      | CHK: DATE:  | TITLE:             |
| SS 7/18/97  | 481   | WM 7/18/97      | BEL 7/17/97 | DIM. OUTLINE DWG.  |
| SCALE: NONE |       | DOC. REL. DATE: | ENG: DATE:  | ESS 10KW STD.      |
|             |       | GFS 7/17/97     | SS 7/17/97  |                    |
|             |       | APP: DATE:      | DWG. NO.    | REV.               |
|             |       | GFS 7/17/97     | 02-481-011  | C                  |