




Features

- (1) For equipment designed to conform EMI regulations such as VCCI, CISPR, FCC, VDE, etc.
- (2) Attenuates conductive emission from power supply
- (3) Leakage current: 1mA max. (250V, 60Hz)
- (4) Compact and light weight

Safety standard


- UL1283, CSA Std. C22. 2 No. 8
- VDE0565 Teil. 3

Specifications


Item	Model	PBW-1201-33	PBW-1202-33	PBW-1203-33	PBW-1206-33
1. Rated voltage (AC, DC)		250V			
2. Rated current (AC, DC)	(Note)	1A	2A	3A	6A
3. Test voltage (terminal to case, AC 1 minute)		1500V			
4. Isolation resistance (terminal to case, 500VDC)		100MΩ min.			
5. Leakage current	125V, 60Hz	0.35mA max.			
	250V, 60Hz	0.75mA max.			
6. DC resistance		1.2Ω max.	0.4Ω max.	0.25Ω max.	0.12Ω max.
7. Temperature rise		30°C max.			
8. Operating temperature range		-25 ~ +85°C			
9. Weight	(typ)	60g	60g	60g	60g

(Note) : Value at Ta ≤ 55°C. Refer to the derating curve shown below at Ta > 55°C.



Circuit



Derating



Outline drawings



Case: Plastic (PBT: UL94V-0)


(Unit: mm)

- Request customer specification for further details of specifications, outline, characteristics, etc.
- Read the instruction manual before usage.
- Contact us about delivery before ordering.


CHARACTERISTICS

■ Typical Insertion Loss Symmetrical
 ——— Asymmetrical


PBW-1201-33




PBW-1202-33



PBW-1203-33



PBW-1206-33



Noise Filter