





| APPLICATION |            |      | LTR | E.C.O. NO.               | BY     | APP. |
|-------------|------------|------|-----|--------------------------|--------|------|
| USED ON     | NEXT ASSY. | QTY. | A   | REL TO MFG.              | 3/94   | WJW  |
|             |            |      | B   | ADDED DIMS REAR VIEW RHS | 7/8/97 | GFS  |
|             |            |      | C   | ECO 16952 1/7/97         | RHS    |      |



- STANDARD FEATURES:
1. U/L RECOGNIZED INPUT CIRCUIT BREAKER.
  2. ANALOG VOLTMETER AND AMMETER.
  3. VOLTAGE AND CURRENT ADJUST.
  4. VOLTAGE AND CURRENT MODE LAMP INDICATORS.
  5. INTERNAL LINE FILTER.
  6. PWM CONTROL.
  7. REMOTE TURN ON AC,DC, OR DRY SWITCH
  8. P/S WEIGHT = 107 LBS.

| AC INPUT CHART |           |
|----------------|-----------|
| TB1            | 3Ø        |
| 1              | L1 INPUT  |
| 2              | L2 INPUT  |
| 3              | L3 INPUT  |
| 4              | N NEUTRAL |
| 5              | GROUND    |

(USED ON 380VAC INPUT ONLY)



|      |             |                  |                    |                   |                                        |
|------|-------------|------------------|--------------------|-------------------|----------------------------------------|
| MTL: | TOL: ±.031  | PRJ: SS 7/17/97  | ENG: DATE: 7/17/97 | DWN: DATE: 9/3/92 | ELECTRONIC MEASUREMENTS, INC.          |
| FIN: | P/L: 481    | MFG: WM 7/18/97  | CHK: BEL 7/17/97   | DATE: 7/17/97     |                                        |
|      | SCALE: NONE | DOC: GFS 7/17/97 | ENG: DATE: 7/17/97 | DATE: 7/17/97     | TITLE: DIM. OUTLINE DWG. ESS 15KW STD. |
|      |             |                  | APP: GFS 7/17/97   | DATE: 7/17/97     | DWG. NO. 02-481-010                    |
|      |             |                  |                    |                   | REV. C                                 |