




APPLICATION			LTR	E.C.O. NO.	BY	APP.
USED ON	NEXT ASSY.	QTY.	A	REL TO MFG.	3/94	WJW
			B	DIMS ADDED/REAR VIEW	7/97	GFS
			C	ECO16952	12/17/97	RHS




- STANDARD FEATURES:
1. U/L RECOGNIZED INPUT CIRCUIT BREAKER.
 2. ANALOG VOLTMETER AND AMMETER.
 3. VOLTAGE AND CURRENT ADJUST.
 4. VOLTAGE AND CURRENT MODE LAMP INDICATORS.
 5. INTERNAL LINE FILTER.
 6. PWM CONTROL.
 7. REMOTE TURN ON AC,DC, OR DRY SWITCH
 8. P/S WEIGHT = 107 LBS.

(4) 8-32 PEMNUTS EACH SIDE FOR CHASSIS
SLIDE OPTION (JONATHAN MFG #370-22)

AC INPUT CHART	
TB1	3ø
1	L1 INPUT
2	L2 INPUT
3	L3 INPUT
4	N NEUTRAL
5	GROUND

(USED ON 380VAC INPUT ONLY)



MTL:	TOL:	PRJ: ENG: DATE:	DWN: DATE:	
FIN:	P/L:	SS 7/18/97	JKA 9/3/92	
	SCALE: NONE	WM 7/18/97	GFS 8-3-95	
		GFS 7/17/97	S 2 8-8-95	
		APP: 7/28/95	ENG: 8-8-95	
			DWG. NO. 02-481-004	
			REV. C	