




APPLICATION			LTR	E.C.O. NO.	BY	APP.
USED ON	NEXT ASSY.	QTY.	A	REL TO MFG. 4/94	JJR	
			B	ADDED DIM/REAR VIEW 7/18/97	RHS	
			C	ECO16952 12/18/97	RHS	



- STANDARD FEATURES:
1. U/L RECOGNIZED INPUT CIRCUIT BREAKER.
 2. ANALOG VOLTMETER AND AMMETER.
 3. VOLTAGE AND CURRENT ADJUST.
 4. VOLTAGE AND CURRENT MODE LAMP INDICATORS.
 5. INTERNAL LINE FILTER.
 6. PWM CONTROL.
 7. REMOTE TURN ON AC,DC, OR DRY SWITCH
 8. P/S WEIGHT = 107 LBS.

AC INPUT CHART	
TB1	3Ø
1	L1 INPUT
2	L2 INPUT
3	L3 INPUT
4	N NEUTRAL
5	GROUND

(USED ON 380VAC INPUT ONLY)



MTL:	TOL:	PRJ: ENG:	DATE:	DWN:	DATE:		ELECTRONIC MEASUREMENTS, INC.
FIN:	±.031	S 2	7/17/97	JKA	9/3/92		
		MFG. WM	7/18/97	CHK: BEL	7/17/97		
		DOC. REL. S2	7/17/97	ENG: S2	7/18/97		
		SCALE: NONE		APP: GFS	7/17/97		
						TITLE: DIM. OUTLINE DWG. ESS 15KW STD.	
						DWG. NO. 02-481-008	REV. C